

Low Noise Metallurgical Sample Polisher Mutifunction for Materials Polishing



Product Details:	
Place of Origin:	China
Brand Name:	HUATEC
Model Number:	PG Series
Payment & Shipp	ing Terms:
Minimum Order Q	uantity: 1 SET
Packaging Details	:: Wooden Case
Delivery Time:	7-10 days
Payment Terms:	TT
r dyment renns.	
Chat Now	

Large Image : Low Noise Metallurgical Sample Polisher Mutifunction for Materials Polishing

Detailed Product Description

Low Noise Metallurgical Sample Polisher Mutifunction for Materials Polishing

Description:

During Metallurgical Sample preparation, polishing is primary. After polishing grinded samples, we can get very bright surface like mirror.PG-1 was designed after collecting many customers' suggestions.PG-1 operates steadily in low noise, and easily to use and maintain. The size of the polishing wheel and the transmission power are bigger than other products in china.PG-1 can adjust to all kinds of materials polishing work.

Main parameters Polishing Wheel Diameter:220mm Platen speed:900rpm,1400rpm(custom-made) Electromotor:YS7116 0.2kW 380V/220V 50Hz The Total Dimensions:325×325×320mm The Net Weight:14Kg

2. PG-1A Metallurgical Sample Polisher





Description:

During Metallurgical Sample preparation, polishing is very primary. After polishing grinded samples, we can get very bright surface like mirror. Collecting many customers' suggestions, PG-1A as designed. PG-1A operates steadily in low noise, and easily to use and maintain. The size of the polishing wheel and the transmission power are bigger. PG-1 adjusts to all kinds of materials polishing work. PG-1A is equipped with polishing water supply system. PG-1A is the ideal equipment for metallurgical sample polishing.

Main parameters

Polishing Wheel Diameter:220mm Platen speed:900rpm,1400rpm(custom-made) Electromotor:YS7116 0.2kW 380V 50Hz The Total Dimensions:460x340x330mm The Net Weight:22Kg



1. PG-2 Metallurgical Sample Polisher



Description:



PG-2 was designed after collecting many customers' suggestions.PG-2 has nice appearance,logical structure, low noise, and it is easy to operate and maintain.PG-2 can be used for 2 persons at the same time.The size of the polishing wheel and the transmission power are bigger than other products in China.PG-2 can adjust to all kinds of materials polishing work.PG-2 is the ideal equipment for metallurgical sample polishing.PG-2 has 2 types, floor type and table type, for choice.

Main parameters Polishing Wheel Diameter:Dual wheels 220mm Platen speed:900rpm,1400rpm(custom-made) Electromotor:YS7116 0.2kW 380V/220V 50Hz The Total Dimensions:800×420×920mm The Net Weight:38Kg



1. PG-2A Metallurgical Sample Polisher

Description:

PG-2A was designed after collecting many customers' suggestions.PG-2A has nice appearance,logical structure,low noise,and it is easy to operate and maintain.PG-2A can be used for 2 persons at the same time.The size of the polishing wheel and the transmission power are bigger than other products in China.PG-2A can adjust to all kinds of materials polishing work.PG-2 is the ideal equipment for metallurgical sample polishing.PG-2A has 2 types, floor type and table type,for choice.

Main parameters Polishing Wheel Diameter:Dual wheels 220mm Platen speed:900rpm,1400rpm(custom-made) Dual speed:900/1400rpm



Electromotor:YS7116 0.2kW 380V/220V 50Hz The Total Dimensions:800×420×200mm The Net Weight:33Kg